


HOLEX**Wheel brush with shank Brass wire 0.20 mm., Brush \varnothing D1 \times bristle width L1: 40X10mm****Order data**

Order number	574360 40X10
GTIN	4067263934813
Item class	57H

Description**Version:**

Waved special high quality wire, **shank \varnothing 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For heavy-duty deburring and brushing of non-ferrous metals

Technical description

Shank \varnothing D _s	6 mm
maximum speed	18000 min ⁻¹
Bristle width L ₁	10 mm
Bristle thickness	0.2 mm
Brush \varnothing D ₁	40 mm
Length of brush section H ₁	9 mm

Brush material	Brass wire
Twisted knotting	waved
Type of product	Wheel brush