


**HOLEX****Wheel brush with shank Brass wire 0.20 mm., Brush  $\varnothing$  D1  $\times$  bristle width L1: 70X10mm****Order data**

Order number	574360 70X10
GTIN	4067263934837
Item class	57H

**Description****Version:**

Waved special high quality wire, **shank  $\varnothing$  6 mm.**

**Application:**

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For heavy-duty deburring and brushing of non-ferrous metals

**Technical description**

maximum speed	15000 min <sup>-1</sup>
Bristle width L <sub>1</sub>	11 mm
Brush $\varnothing$ D <sub>1</sub>	70 mm
Length of brush section H <sub>1</sub>	19 mm
Shank $\varnothing$ D <sub>s</sub>	6 mm
Bristle thickness	0.2 mm

Brush material	Brass wire
Twisted knotting	waved
Type of product	Wheel brush