

Garant**Turning insert, medium machining CNMG, HB7020, Size / quantity: 09T308/50****Order data**

Order number	GG2527 09T308/50
GTIN	4067263092285
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 3.25 mm
Feed f	0.25 - 0.4 mm/rev.
Cutting speed v_c main application	130 - 280 mm/min
Quantity	50
Contents	250152 HB7020
ISO code indexable insert	CNMG09T308
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

CNMG 09T308 Grade HB7020

250152 HB7020