

HOLEX

Wheel brush with shank Stainless steel wire 0.20 mm, Brush \varnothing D1 \times bristle width L1: 80X12mm



Order data

Order number	574253 80X12
GTIN	4067263934790
Item class	57H

Description

Version:

Waved special high quality wire, **shank \varnothing 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

Technical description

Length of brush section H ₁	20 mm
Brush width	12 mm
Brush \varnothing D ₁	80 mm
Shank \varnothing D _s	6 mm
Bristle width L ₁	9 mm
maximum speed	15000 min ⁻¹

Bristle thickness	0.2 mm
Brush material	Stainless steel wire
Twisted knotting	waved
Type of product	Wheel brush