

**Garant****Turning insert, medium machining CNMG, HB7020, Size / quantity: 09T304/30****Order data**

Order number	GG2527 09T304/30
GTIN	4067263092254
Item class	GGN

**Technical description**

Feed f	0.25 - 0.4 mm/rev.
Contents	250150 HB7020
Cutting depth $a_p$	0.25 - 3.25 mm
Cutting speed $v_c$ main application	130 - 280 mm/min
Quantity	30
ISO code indexable insert	CNMG09T304
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

CNMG 09T304 Grade HB7020

250150 HB7020