


HOLEX**Wheel brush with shank Brass wire 0.20 mm., Brush \varnothing D1 \times bristle width L1: 70X16mm****Order data**

Order number	574360 70X16
GTIN	4067263934844
Item class	57H

Description**Version:**

Waved special high quality wire, **shank \varnothing 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For heavy-duty deburring and brushing of non-ferrous metals

Technical description

Length of brush section H ₁	19 mm
Bristle width L ₁	16 mm
Bristle thickness	0.2 mm
Shank \varnothing D _s	6 mm
Brush \varnothing D ₁	70 mm
maximum speed	15000 min ⁻¹

Brush material	Brass wire
Twisted knotting	waved
Type of product	Wheel brush