

**End brush Steel wire 0.30 mm, Type: 10X20****Order data**

Order number	574550 10X20
GTIN	4067263935056
Item class	57H

**Description****Version:**

Waved special high quality wire, crimped into steel ferrule, **shank Ø 6 mm.**

**Application:**

For straight die grinders, on flexible drive machines and drills. For cleaning and deburring at inaccessible places.

**Technical description**

Brush Ø D <sub>1</sub>	12 mm
maximum speed	20000 min <sup>-1</sup>
Clamp length L <sub>2</sub>	20 mm
Overall length L	67 mm
Clamp Ø D <sub>2</sub>	10 mm
Length of brush section H <sub>1</sub>	20 mm
Type of product	End brush