


HOLEX**Turning insert, medium machining CNMG, HBT020, Size / quantity: 09T304/50**

Order data

Order number	GG2530 09T304/50
GTIN	4067263092483
Item class	GGN

Technical description

Cutting depth a_p	0.25 - 3.25 mm
Feed f	0.2 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 240 mm/min
Quantity	50
Contents	250188 HBT020
ISO code indexable insert	CNMG09T304
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

CNMG 09T304 Grade HBT020

250188 HBT020