


**End brush Steel wire 0.30 mm, Type: 22X22****Order data**

Order number	574550 22X22
GTIN	4067263935063
Item class	57H

Description**Version:**

Waved special high quality wire, crimped into steel ferrule, **shank Ø 6 mm.**

Application:

For straight die grinders, on flexible drive machines and drills. For cleaning and deburring at inaccessible places.

Technical description

Brush Ø D ₁	23 mm
Clamp Ø D ₂	22 mm
Clamp length L ₂	22 mm
Overall length L	80 mm
Length of brush section H ₁	25 mm
maximum speed	18000 min ⁻¹
Type of product	End brush

