

Garant**Turning insert, roughing CNMG, HB7020, Size / quantity: 190624/30****Order data**

Order number	GG2531 190624/30
GTIN	4067263092711
Item class	GGN

Technical description

Cutting speed v_c main application	100 - 260 mm/min
Contents	250343 HB7020
Feed f	0.3 - 0.5 mm/rev.
Cutting depth a_p	1.6 - 6.75 mm
Quantity	30
ISO code indexable insert	CNMG190624
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

CNMG 190624 Grade HB7020

250343 HB7020