

**Garant****Turning insert, roughing CNMG, HB7020, Size / quantity: 190616/50****Order data**

Order number	GG2531 190616/50
GTIN	4067263092704
Item class	GGN

**Technical description**

Cutting depth $a_p$	1.6 - 6.75 mm
Feed $f$	0.3 - 0.5 mm/rev.
Cutting speed $v_c$ main application	100 - 260 mm/min
Quantity	50
Contents	250341 HB7020
ISO code indexable insert	CNMG190616
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

## Accessories

CNMG 190616 Grade HB7020

250341 HB7020