


**Turning insert, roughing CNMG, HBT020, Size / quantity: 160612/30****Order data**

Order number	GG2534 160612/30
GTIN	4067263092797
Item class	GGN

Technical description

Feed f	0.3 - 0.5 mm/rev.
Cutting speed v_c main application	100 - 220 mm/min
Contents	250221 HBT020
Cutting depth a_p	0.8 - 5.5 mm
Quantity	30
ISO code indexable insert	CNMG160612
Grade	HBT020
Chip breaker	PR
Type of product	Indexable insert for turning

Accessories

CNMG 160612 Grade HBT020

250221 HBT020