



**Turning insert, medium machining DNMG, HBT020, Size / quantity:
110404/30**



Order data

Order number	GG2538 110404/30
GTIN	4067263092919
Item class	GGN

Technical description

Cutting depth a_p	0.25 - 2.75 mm
Feed f	0.2 - 0.3 mm/rev.
Contents	250780 HBT020
Cutting speed v_c main application	120 - 240 mm/min
Quantity	30
ISO code indexable insert	DNMG110404
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

DNMG 110404 Grade HBT020

250780 HBT020