

**Garant**

**Turning insert, medium machining DNMG, HB7020, Size / quantity:  
150612/50**

**Order data**

Order number	GG2535 150612/50
GTIN	4067263092902
Item class	GGN

**Technical description**

Feed f	0.25 - 0.4 mm/rev.
Cutting speed $v_c$ main application	125 - 280 mm/min
Cutting depth $a_p$	0.8 - 3.75 mm
Quantity	50
Contents	250764 HB7020
ISO code indexable insert	DNMG150612
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

---

## Accessories

DNMG 150612 Grade HB7020

250764 HB7020