

**Garant**

**Turning insert, medium machining DNMG, HB7020, Size / quantity:  
110408/30**

**Order data**

Order number	GG2535 110408/30
GTIN	4067263092834
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.55 - 2.75 mm
Feed $f$	0.25 - 0.4 mm/rev.
Contents	250754 HB7020
Cutting speed $v_c$ main application	125 - 280 mm/min
Quantity	30
ISO code indexable insert	DNMG110408
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

---

## Accessories

DNMG 110408 Grade HB7020

250754 HB7020