

Garant
End milling head, 45° chamfer with IC, HB730, Ø D h10: 12mm

Order data

Order number	210100 12
GTIN	4045197557292
Item class	21M

Description
Note:

Standard application values for $a_{p\max} \leq 0.5 \times D$.

Technical description

Head length l	16 mm
Flute length L_2	9 mm
Cutter Ø D	12 mm
Corner chamfer width at 45°	0.24 mm
Feed f_z for side milling in steel < 900 N/mm ²	0.07 mm
Feed f_z for slot milling in steel < 900 N/mm ²	0.05 mm
Arbor size	12 mm
Corner chamfer angle	45 degrees
Series	TopCut
Grade	HB730
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N

Spacing of the cutters	unequal spacing
Helix angle	40 degrees
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.3×D for side milling mm
Cutting width a_e for milling operation	Full slot cutting depth 1×D mm
Machining strategy	HPC
Through-coolant	yes
suitable arbor	GARANT TopCut
Type of product	Cutter insert for milling

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	210 m/min	P
Steel < 750 N/mm ²	suitable	170 m/min	P
Steel < 900 N/mm ²	suitable	150 m/min	P
Steel < 1100 N/mm ²	suitable	130 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	110 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	50 m/min	H
Steel < 60 HRC	suitable only under restricted conditions	40 m/min	H
INOX < 900 N/mm ²	suitable	80 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	50 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	80 m/min	S
GG(G)	suitable	160 m/min	K
Oil	suitable only under restricted conditions		
wet maximum	suitable		

wet minimum	suitable only under restricted conditions
dry	suitable only under restricted conditions
Air	suitable

Accessories

Plug-in adapter for torque wrench Type 10X4	219986 10X4
Assembly wrench Type 10X4	219987 10X4