



**Turning insert, medium machining DNMG, HBT020, Size / quantity:
110408/30**



Order data

| | |
|--------------|------------------|
| Order number | GG2538 110408/30 |
| GTIN | 4067263092933 |
| Item class | GGN |

Technical description

| | |
|--------------------------------------|------------------------------|
| Cutting speed v_c main application | 120 - 240 mm/min |
| Cutting depth a_p | 0.55 - 2.75 mm |
| Contents | 250781 HBT020 |
| Feed f | 0.2 - 0.3 mm/rev. |
| Quantity | 30 |
| ISO code indexable insert | DNMG110408 |
| Grade | HBT020 |
| Chip breaker | PM |
| Type of product | Indexable insert for turning |

Accessories

DNMG 110408 Grade HBT020

250781 HBT020