



Cordless belt file, Type: M12FBFL10



Order data

Order number	077717 M12FBFL10
GTIN	4058546412432
Item class	03L

Description

Version:

Extremely light cordless belt file (only 1.0 kg or 1.1 kg with a 2 Ah battery) for fatigue-free working.

- **Two speed modes + variable speed controller.**
- **Reverse mode – allows the user to select the belt orientation to control the direction of sparks/chips.**
- **360° head adjustment without the need for tools.**
- **One-handed operation – enables the user to work in confined areas and is ideal for overhead working.**

Supplied with:

Without battery and without charger.

Note:

See 073814 ff. for suitable batteries and chargers.

Technical description

maximum vibration to EN	2.16 m/s ²
Number of rechargeable batteries contained	0
Finishing belt width	10 mm
Type of rechargeable battery	Lithium-ion
Battery voltage	12 V

Power supply	Mains operated
Belt speed	0 - 1110 m/min
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Manufacturer's designation	M12 FBFL10
Weight	1 kg
Speed range	0 - 14500 min ⁻¹
Linishing belt length	330
Type of product	Electric file