

Garant**Turning insert, roughing DNMG, HB7020, Size / quantity: 150608/30****Order data**

Order number	GG2539 150608/30
GTIN	4067263092995
Item class	GGN

Technical description

Contents	250862 HB7020
Feed f	0.3 - 0.5 mm/rev.
Cutting depth a_p	0.55 - 3.75 mm
Cutting speed v_c main application	105 - 260 mm/min
Quantity	30
ISO code indexable insert	DNMG150608
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

DNMG 150608 Grade HB7020

250862 HB7020