


**CNMG 120412 DNMG, HBT020, Size / quantity: 150612/30****Order data**

Order number	GG2542 150612/30
GTIN	4067263093053
Item class	GGN

Technical description

Cutting speed v_c main application	100 - 200 mm/min
Contents	250787 HBT020
Cutting depth a_p	0.8 - 3.75 mm
Feed f	0.3 - 0.5 mm/rev.
Quantity	30
ISO code indexable insert	DNMG150612
Grade	HBT020
Chip breaker	PR
Type of product	Indexable insert for turning

Accessories

DNMG 150612 Grade HBT020

250787 HBT020