




Centring vice, Width: 120mm



Order data

Order number	363300 120
GTIN	4067263950684
Item class	30N

Description

Version:

- **Very good accessibility and perfectly symmetrical.**
- **Fully plasma-nitrided and precision milled on the underside.**
- **Clamps raw materials and finished parts with the least possible backstroke of the jaws / component.**
- **The clamping range can be changed by reversing the jaws.**
- **With interface for automated applications.**
- **Including holes for LANG positioning system, can be adapted to GARANT ZeroClamp and Erowa ITS148 (only No. 363300 75) via intermediate plate.**

Application:

Perfect for 5-face machining. Centred clamping.

Suitable for:

Top jaws No. 363310 – 363324.

Supplied with:

Base body, spindle, spindle nuts.

Optional extras:

Torque wrench No. 656050, socket No. 642229 12 (for size 75), No. 642229 13 (for size 120) clamping claws No. 363081 80 and 361165 CS1, GARANT clamping stud No. 363190, adapter plates No. 363079, 363080, 363085 height extension base No. 363090 (in combination with No. 363079) assembly station No. 358595 52/96.

Note:

Suitable top jaws No. 363310 – 363324 are not included in the scope of supply. Clamping situation S2 arises by reversing the jaws.

Technical description

Weight	9.5 kg
B	125 mm
Width	120 mm
Height H	65 mm
L	180 mm
maximum clamping force	28 kN
maximum tightening torque	100 Nm
Colour code	HOLEX ZS 120
Reference dimension	96 mm
Type of product	Machine vice