

Garant**Turning insert, roughing DNMG, HB7020, Size / quantity: 150608/50****Order data**

Order number	GG2539 150608/50
GTIN	4067263093008
Item class	GGN

Technical description

Feed f	0.3 - 0.5 mm/rev.
Cutting depth a_p	0.55 - 3.75 mm
Cutting speed v_c main application	105 - 260 mm/min
Quantity	50
Contents	250862 HB7020
ISO code indexable insert	DNMG150608
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

DNMG 150608 Grade HB7020

250862 HB7020