

Garant**Turning insert, roughing DNMG, HB7020, Size / quantity: 150612/50****Order data**

Order number	GG2539 150612/50
GTIN	4067263093022
Item class	GGN

Technical description

Feed f	0.3 - 0.5 mm/rev.
Cutting speed v_c main application	105 - 260 mm/min
Cutting depth a_p	0.8 - 3.75 mm
Quantity	50
Contents	250864 HB7020
ISO code indexable insert	DNMG150612
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

DNMG 150612 Grade HB7020

250864 HB7020