

Garant**Turning insert, medium machining SNMG, HB7020, Size / quantity: 120412/30****Order data**

Order number	GG2544 120412/30
GTIN	4067263093114
Item class	GGN

Technical description

Cutting speed v_c main application	130 - 280 mm/min
Feed f	0.2 - 0.4 mm/rev.
Cutting depth a_p	0.8 - 4.25 mm
Contents	251226 HB7020
Quantity	30
ISO code indexable insert	SNMG120412
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

SNMG 120412 Grade HB7020

251226 HB7020