


Garant**Turning insert, medium machining SNMG, HB7020, Size / quantity: 150612/50**

Order data

Order number	GG2544 150612/50
GTIN	4067263093169
Item class	GGN

Technical description

Feed f	0.2 - 0.4 mm/rev.
Cutting speed v_c main application	130 - 280 mm/min
Cutting depth a_p	0.8 - 5.25 mm
Quantity	50
Contents	251232 HB7020
ISO code indexable insert	SNMG150612
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

SNMG 150612 Grade HB7020

251232 HB7020