


Garant**Turning insert, medium machining SNMG, HB7020, Size / quantity: 120408/50****Order data**

Order number	GG2544 120408/50
GTIN	4067263093107
Item class	GGN

Technical description

Cutting speed v_c main application	130 - 280 mm/min
Cutting depth a_p	0.55 - 4.25 mm
Feed f	0.2 - 0.4 mm/rev.
Quantity	50
Contents	251224 HB7020
ISO code indexable insert	SNMG120408
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

SNMG 120408 Grade HB7020

251224 HB7020