

**Value pack turning insert roughing SNMG****Order data**

Order number	GG2549 150612/50
GTIN	4067263093305
Item class	GGN

Technical description

Cutting depth a_p	0.8 - 5.25 mm
Cutting speed v_c main application	105 - 260 mm/min
Feed f	0.3 - 0.5 mm/rev.
Quantity	50
Contents	251330 HB7020
ISO code indexable insert	SNMG150612
Type	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG2549-150612/50>