

Garant**Turning insert, medium machining TNMG, HB7020, Size / quantity: 160408/30****Order data**

| | |
|--------------|------------------|
| Order number | GG2555 160408/30 |
| GTIN | 4067263093411 |
| Item class | GGN |

Technical description

| | |
|--------------------------------------|------------------------------|
| Contents | 251544 HB7020 |
| Cutting depth a_p | 0.55 - 4 mm |
| Feed f | 0.2 - 0.4 mm/rev. |
| Cutting speed v_c main application | 130 - 280 mm/min |
| Quantity | 30 |
| ISO code indexable insert | TNMG160408 |
| Grade | HB7020 |
| Chip breaker | SM |
| Type of product | Indexable insert for turning |

Accessories

TNMG 160408 Grade HB7020

251544 HB7020