

**Garant****Turning insert, medium machining TNMG, HB7020, Size / quantity: 160404/30****Order data**

Order number	GG2555 160404/30
GTIN	4067263093398
Item class	GGN

**Technical description**

Contents	251542 HB7020
Cutting speed $v_c$ main application	130 - 280 mm/min
Cutting depth $a_p$	0.25 - 4 mm
Feed $f$	0.2 - 0.4 mm/rev.
Quantity	30
ISO code indexable insert	TNMG160404
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

**Accessories**

TNMG 160404 Grade HB7020

251542 HB7020