

**Garant****Turning insert, roughing WNMG, HB7020, Size / quantity: 080412/30****Order data**

|              |                  |
|--------------|------------------|
| Order number | GG2568 080412/30 |
| GTIN         | 4067263093732    |
| Item class   | GGN              |

**Technical description**

|                                      |                              |
|--------------------------------------|------------------------------|
| Cutting speed $v_c$ main application | 85 - 260 mm/min              |
| Feed $f$                             | 0.3 - 0.5 mm/rev.            |
| Contents                             | 252210 HB7020                |
| Cutting depth $a_p$                  | 0.8 - 2.75 mm                |
| Quantity                             | 30                           |
| ISO code indexable insert            | WNMG080412                   |
| Grade                                | HB7020                       |
| Chip breaker                         | SG                           |
| Type of product                      | Indexable insert for turning |

**Accessories**

WNMG 080412 Grade HB7020

252210 HB7020