


**Turning insert, roughing WNMG, HBT020, Size / quantity: 080412/50****Order data**

Order number	GG2570 080412/50
GTIN	4067263093787
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	100 - 220 mm/min
Feed $f$	0.3 - 0.5 mm/rev.
Cutting depth $a_p$	0.8 - 2.75 mm
Quantity	50
Contents	252226 HBT020
ISO code indexable insert	WNMG080412
Grade	HBT020
Chip breaker	PR
Type of product	Indexable insert for turning

**Accessories**

WNMG 080412 Grade HBT020

252226 HBT020