

Garant**Value pack turning insert medium machining CNMG, Size / quantity:
160608/50**

Order data

Order number	GG2571 160608/50
GTIN	4067263093909
Item class	GGN

Technical description

Cutting speed v_c main application	90 - 170 mm/min
Feed f	0.2 - 0.4 mm/rev.
Contents	250168 HB7130-2
Cutting depth a_p	0.55 - 5.5 mm
Quantity	50
ISO code indexable insert	CNMG160608
Grade	HB7130-2
Chip breaker	VM
Type of product	Indexable insert for turning

Accessories

CNMG 160608 Grade HB7130-2

250168 HB7130-2