

**HOLEX****Turning insert, medium machining CNMG, HBT130, Size / quantity: 160608/50****Order data**

Order number	GG2573 160608/50
GTIN	4067263094029
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	90 - 135 mm/min
Contents	250204 HBT130
Feed $f$	0.2 - 0.3 mm/rev.
Cutting depth $a_p$	0.55 - 5.5 mm
Quantity	50
ISO code indexable insert	CNMG160608
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

## Accessories

CNMG 160608 Grade HBT130

250204 HBT130