

**Value pack turning insert roughing CNMG, Size / quantity: 160608/50****Order data**

Order number	GG2576 160608/50
GTIN	4067263094203
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 5.5 mm
Feed f	0.3 - 0.5 mm/rev.
Contents	250220 HBT130
Cutting speed v_c main application	70 - 120 mm/min
Quantity	50
ISO code indexable insert	CNMG160608
Grade	HBT130
Chip breaker	MR
Type of product	Indexable insert for turning

Accessories

CNMG 160608 Grade HBT130

250220 HBT130