

Garant

**GARANT Softcut® 90° shoulder mill MTC, with bore, Ø D / number of teeth Z:
125/8mm**


Order data

Order number	215160 125/8
GTIN	4045197349378
Item class	210

Description
Version:

High precision square shoulder milling cutter with irregular pitch for very smooth cutting, very high precision and cutting power. High performance indexable square shoulder milling cutter **with special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or **for spindles with low drive power**.

Application:

For corner milling to large depths, also slotting. General use in all steels including stainless steels. Especially for **MTC (Multi Task Cutting)** use on the new generation of turning / milling centres (MTM).

Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.
The insert pocket must be modified when using indexable inserts with a radius greater than 3.1 mm.

Technical description

suitable indexable insert	AP.. 1805..
---------------------------	-------------

Overall length L_{tot}	63 mm
Cutting edge $\varnothing D_c$	125 mm
Mounting bore \varnothing	40 mm
Pack of insert screws	219808 (15IP; 3.8 Nm)
Number of cutting edges Z	8
Ramping angle α_{max}	0.24 degrees
Circular interpolation milling a_p	0.85 mm
Ramping length L for α_{max}	116.95 mm
Circular interpolation milling $\varnothing D_{min}$	244 mm
Circular interpolation milling $\varnothing D_{max}$	248 mm
Series	Softcut®
$\varnothing D_3$	119 mm
Shank type	with bore
Setting angle κ	90 degrees
Milling application	Corner milling
Milling application	Circular milling
Milling application	Ramping
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8
Set of insert screws 10-piece	219808

