


Garant**Turning insert, roughing CNMG, HB7130-2, Size / quantity: 160612/50****Order data**

Order number	GG2574 160612/50
GTIN	4067263094128
Item class	GGN

Technical description

Cutting speed v_c main application	90 - 170 mm/min
Cutting depth a_p	0.8 - 5.5 mm
Contents	250336 HB7130-2
Feed f	0.35 - 0.45 mm/rev.
Quantity	50
ISO code indexable insert	CNMG160612
Grade	HB7130-2
Chip breaker	VG
Type of product	Indexable insert for turning

Accessories

CNMG 160612 Grade HB7130-2

250336 HB7130-2