

**Value pack turning insert roughing CNMG****Order data**

Order number	GG2576 160612/50
GTIN	4067263094227
Item class	GGN

**Technical description**

Quantity	50
Cutting speed $v_c$ main application	70 - 120 mm/min
Contents	250221 HBT130
Cutting depth $a_p$	0.8 - 5.5 mm
Feed $f$	0.3 - 0.5 mm/rev.
ISO code indexable insert	CNMG160612
Type	HBT130
Chip breaker	MR
Type of product	Indexable insert for turning

**Suitable products**

<https://www.hoffmann-group.com/GB/en/hom/p/GG2576-160612/50>

