



**Turning insert, medium machining DNMG, HBT130, Size / quantity:  
110408/50**



### Order data

Order number	GG2579 110408/50
GTIN	4067263094364
Item class	GGN

### Technical description

Cutting depth $a_p$	0.55 - 2.75 mm
Cutting speed $v_c$ main application	80 - 135 mm/min
Feed $f$	0.2 - 0.3 mm/rev.
Contents	250781 HBT130
Quantity	50
ISO code indexable insert	DNMG110408
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

---

## Accessories

DNMG 110408 Grade HBT130

250781 HBT130