

Garant**Turning insert, roughing DNMG, HB7130-2, Size / quantity: 150612/30****Order data**

Order number	GG2580 150612/30
GTIN	4067263094418
Item class	GGN

Technical description

Cutting speed v_c main application	90 - 170 mm/min
Contents	250864 HB7130-2
Cutting depth a_p	0.8 - 3.75 mm
Feed f	0.35 - 0.45 mm/rev.
Quantity	30
ISO code indexable insert	DNMG150612
Grade	HB7130-2
Chip breaker	VG
Type of product	Indexable insert for turning

Accessories

DNMG 150612 Grade HB7130-2

250864 HB7130-2