

Garant

**Turning insert, medium machining KNUX, HB7020, Size / quantity:
160405R/50**

**Order data**

Order number	GG2541 160405R/50
GTIN	4067263094562
Item class	GGN

Technical description

Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.35 - 4 mm
Cutting speed v_c main application	120 - 250 mm/min
Quantity	50
Contents	251030 HB7020
ISO code indexable insert	KNUX160405
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

KNUX 160405R Grade HB7020	251030 HB7020
---------------------------	---------------