

**Turning insert, medium machining TNMG, HBT130, Size / quantity: 160404/30****Order data**

Order number	GG2588 160404/30
GTIN	4067263094777
Item class	GGN

Technical description

Quantity	30
Feed f	0.2 - 0.3 mm/rev.
Cutting depth a_p	0.25 - 4 mm
Cutting speed v_c main application	80 - 135 mm/min
Contents	251564 HBT130
ISO code indexable insert	TNMG160404
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

TNMG 160404 Grade HBT130

251564 HBT130