

**Turning insert, roughing WNMG, HBT130, Size / quantity: 080408/30****Order data**

Order number	GG2597 080408/30
GTIN	4067263095095
Item class	GGN

Technical description

Feed f	0.3 - 0.5 mm/rev.
Cutting depth a_p	0.55 - 2.75 mm
Quantity	30
Contents	252224 HBT130
Cutting speed v_c main application	70 - 120 mm/min
ISO code indexable insert	WNMG080408
Grade	HBT130
Chip breaker	MR
Type of product	Indexable insert for turning

Accessories

WNMG 080408 Grade HBT130

252224 HBT130