

Garant**Turning insert, medium machining CCMT, HB7020, Size / quantity: 09T302/30****Order data**

Order number	GG2620 09T302/30
GTIN	4067263095170
Item class	GGN

Technical description

Cutting depth a_p	0.15 - 3.25 mm
Feed f	0.1 - 0.25 mm/rev.
Contents	260148 HB7020
Cutting speed v_c main application	130 - 280 mm/min
Quantity	30
ISO code indexable insert	CCMT09T302
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

CC.T 09T302 Grade HB7020

260148 HB7020