

Garant**Turning insert, medium machining CCMT, HB7020, Size / quantity: 09T308/50****Order data**

Order number	GG2620 09T308/50
GTIN	4067263095224
Item class	GGN

Technical description

Feed f	0.1 - 0.25 mm/rev.
Cutting depth a_p	0.55 - 3.25 mm
Cutting speed v_c main application	130 - 280 mm/min
Contents	260152 HB7020
Quantity	50
ISO code indexable insert	CCMT09T308
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

CC.T 09T308 Grade HB7020

260152 HB7020