

**Garant****Turning insert, medium machining DCMT, HB7020, Size / quantity: 11T304/50****Order data**

Order number	GG2624 11T304/50
GTIN	4067263095460
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.25 - 2.75 mm
Feed $f$	0.1 - 0.25 mm/rev.
Contents	260462 HB7020
Cutting speed $v_c$ main application	130 - 280 mm/min
Quantity	50
ISO code indexable insert	DCMT11T304
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

DC.T 11T304 Grade HB7020

260462 HB7020