


**Turning insert, medium machining DCMT, HBT020, Size / quantity: 11T304/50****Order data**

Order number	GG2627 11T304/50
GTIN	4067263095545
Item class	GGN

Technical description

Cutting depth a_p	0.25 - 2.75 mm
Contents	260507 HBT020
Feed f	0.2 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 240 mm/min
Quantity	50
ISO code indexable insert	DCMT11T304
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

DCMT 11T304 Grade HBT020

260507 HBT020