

**Garant****Turning insert, medium machining DCMT, HB7020, Size / quantity: 11T302/50****Order data**

Order number	GG2624 11T302/50
GTIN	4067263095446
Item class	GGN

**Technical description**

Contents	260458 HB7020
Feed f	0.1 - 0.25 mm/rev.
Cutting depth $a_p$	0.15 - 2.75 mm
Cutting speed $v_c$ main application	130 - 280 mm/min
Quantity	50
ISO code indexable insert	DCMT11T302
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

DC.T 11T302 Grade HB7020

260458 HB7020