

Garant**Turning insert, medium machining DCMT, HB7020, Size / quantity: 11T308/50****Order data**

Order number	GG2624 11T308/50
GTIN	4067263095484
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 2.75 mm
Cutting speed v_c main application	130 - 280 mm/min
Feed f	0.1 - 0.25 mm/rev.
Contents	260464 HB7020
Quantity	50
ISO code indexable insert	DCMT11T308
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

DC.T 11T308 Grade HB7020

260464 HB7020