


**Turning insert, medium machining DCMT, HBT020, Size / quantity: 11T308/30****Order data**

Order number	GG2627 11T308/30
GTIN	4067263095552
Item class	GGN

Technical description

Feed f	0.2 - 0.3 mm/rev.
Cutting depth a_p	0.55 - 2.75 mm
Contents	260508 HBT020
Cutting speed v_c main application	120 - 240 mm/min
Quantity	30
ISO code indexable insert	DCMT11T308
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

DCMT 11T308 Grade HBT020

260508 HBT020