

Garant**Turning insert, medium machining TCMT, HB7020, Size / quantity: 16T308/30****Order data**

| | |
|--------------|------------------|
| Order number | GG2632 16T308/30 |
| GTIN | 4067263095774 |
| Item class | GGN |

Technical description

| | |
|--------------------------------------|------------------------------|
| Cutting speed v_c main application | 130 - 280 mm/min |
| Contents | 260988 HB7020 |
| Feed f | 0.1 - 0.25 mm/rev. |
| Cutting depth a_p | 0.55 - 4 mm |
| Quantity | 30 |
| ISO code indexable insert | TCMT16T308 |
| Grade | HB7020 |
| Chip breaker | SM |
| Type of product | Indexable insert for turning |

Accessories

TCMT 16T308 Grade HB7020

260988 HB7020